




# OPTICLEAN®

## 25-Compartment

- Use for large diameter beverage glasses, red wine stems, goblets and most rocks glasses




RG25-1



RG25-1C

Find The Perfect Glass Rack  
[www.carlislefsp.com/FINDRACK](http://www.carlislefsp.com/FINDRACK)



Prod No	Description	Glass Dia**	Glass Height	Color	Pack
<b>25-Compartment OptiClean Glass Rack—Compartment Size 3.54" Square</b>					
RG25 Δ	25-Compartment	3.25"	3.19"	14	6 ea
RG25-1 Δ	25-Compartment with 1 Extender	3.25"	4.75"	14	4 ea
RG25-2 Δ	25-Compartment with 2 Extenders	3.25"	6.34"	14	3 ea
RG25-3 Δ	25-Compartment with 3 Extenders	3.25"	7.94"	14	2 ea
RG25-4 Δ	25-Compartment with 4 Extenders	3.25"	9.5"	14	2 ea
RG25-5 Δ	25-Compartment with 5 Extenders	3.25"	11.1"	14	2 ea
RE25	25-Compartment Divided Extender	3.25"	1.5"	14	6 ea
RE*	Open Extender	—	1.5"	14	6 ea
<b>25-Compartment OptiClean Color-Coded Glass Rack—Compartment Size 3.54" Square</b>					
RG25-1C Δ	25-Compartment with 1 Extender	3.25"	4.75"	410, 411, 412, 413, 414	4 ea
RG25-2C Δ	25-Compartment with 2 Extenders	3.25"	6.34"	410, 411, 412, 413, 414	3 ea
RG25-3C Δ	25-Compartment with 3 Extenders	3.25"	7.94"	410, 411, 412, 413, 414	2 ea
RG25-4C Δ	25-Compartment with 4 Extenders	3.25"	9.5"	410, 411, 412, 413, 414	2 ea
RG25-5C Δ	25-Compartment with 5 Extenders	3.25"	11.1"	410, 411, 412, 413, 414	2 ea
RE25C	25-Compartment Divided Extender	3.25"	1.5"	04, 05, 09, 24, 89	6 ea
RE*	Open Extender	—	1.5"	14	6 ea

NSF Listed products are designated with a Δ and may be prefixed with an N

\*Note: The RE Open Extender can be used with any OptiClean Glass or Dish Rack

\*\*Dimensions shown are for the recommended maximum glass size for the compartment